

TY805K01

ABB Ability™ System 800xA® hardware selector

8 pcs Shunt Stick TY805. 125 + 125 ohms shunt with current limitation. Used for AI845 and AI880A on TU834, TU844, TU845, TU854.



General info

Article number	3BSE081160R1
Mechanics	S800

Environment and certification

CE mark	Yes
Electrical safety	IEC 61131-2, UL 61010-1, UL 61010-2-201
Hazardous Location	C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2
Temperature, Operating	0 to +55 °C (Storage -25 to +70 °C), RH=5 to 95 % no condensation, IEC/EN 61131-2
Pollution degree	Degree 2, IEC 60664-1
Corrosion protection	ISA-S71.04: G3
Protection class	IP20 according to IEC 60529
Mechanical operating conditions	IEC 61131-2
EMC	EN 61000-6-4 and EN 61000-6-2
Overvoltage categories	IEC/EN 60664-1
Equipment class	Class I according to IEC 61140; (earth protected)
RoHS compliance	Directive 2011/65/EU (EN 50581:2012)
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions	
Width	15.5 mm
Depth	62 mm
Height	11 mm
Weight	0.06 kg

solutions.abb/800xA
solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved