

# CB802 Profibus DP Interface

## ABB Ability™ System 800xA® hardware selector

CB802 Profibus DP Communication Interface. PROFIBUS DP slave expansion module for Panel 800 Version 6 panels. Not possible to use for PP880R, PP885H, PP885M, PP885R, PP886R, PP886H, PP887H and PP887S.



### General info

Article number	3BSE069285R1
Operating temperature	-30 °C to +70 °C

### Detailed data

Interaction type	Communication speed: 12000 kbit/s
------------------	-----------------------------------

### Environment and certification

Relative operating humidity	5 % – 95 % non-condensed
Storage temperature	-40 °C to +80 °C
CE-marking	CE
RoHS compliance	DIRECTIVE/2011/65/EU
WEEE compliance	DIRECTIVE/2012/19/EU

### Dimensions

Height	35 mm
Width	130 mm
Weight	0.18 kg

—  
[solutions.abb/800xA](https://solutions.abb/800xA)  
[solutions.abb/controlsystems](https://solutions.abb/controlsystems)

—  
800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2024 ABB All rights reserved