

AI890

ABB Ability™ System 800xA® hardware selector



The AI890 Analog Input Module has 8 channels. The module includes Intrinsic Safety protection components on each channel for connection to process equipment in hazardous areas without the need for additional external devices.

Each channel can be either a current input or power and monitor a two-wire process transmitter. The current input is for externally powered transmitters. The input voltage drop of the current input is typically 3 V, PTC included. The transmitter supply for each channel is able to provide at least 15 V at a 20 mA loop current to power Ex certified process transmitters and is limited to 23 mA in overload conditions. All eight channels are isolated from the ModuleBus and power supply in one group. Power to the input stages is converted from the 24 V on the power supply connections.

TU890 and TU891 Compact MTU can be used with this module and it enables two wire connection to the process devices without additional terminals. TU890 for Ex applications and TU 891 for non Ex applications.

Features and benefits

- 8 channels for 0...20 mA or 4...20 mA, single ended unipolar inputs.
- 1 group of 8 channels isolated from ground.
- Power and monitor for Ex certified two-wire transmitters.
- Non energy-storing analog inputs for externally powered sources.

General info

Article number	3BSC690071R1
Type	Analog Input
Signal specification	0...20 mA
Number of channels	8
Signal type	Unipolar single ended
HART	No
SOE	No
Redundancy	No
High integrity	No
Intrinsic safety	Yes
Mechanics	S800

Detailed data	
Resolution	12 bit
Isolation	Group wise isolated from ground
Under/over range	0 / 22 mA
Error	Max. 0.1%
Temperature drift	Typ. 50 ppm/°C Max. 100 ppm/°C
Input filter (rise time 0-90%)	75 ms
Update cycle time	5 ms
Current limiting	Built in current limited transmitter power
CMRR, 50Hz, 60Hz	>80 dB
NMRR, 50Hz, 60Hz	>20 dB
Rated insulation voltage	50 V
Dielectric test voltage	500 V a.c.
Power dissipation	1.5 W
Current consumption +5 V Modulebus	Typ. 70 mA, Max. 150 mA
Current consumption +24 V external	Typ. 220 mA, Max. <300 mA

Diagnostics	
Front LED's	F(ault), R(un), W(arning)
Supervision	Internal process supply
Status indication of supervision	Module Error, Module Warning, Channel error

Environment and certification	
CE mark	Yes
Electrical safety	EN 61010-1, EN 61010-2-201
Hazardous Location	ATEX/IECEx Zone 2 with interface to Zone 0, cFMus C1, Div 2/Zone 2 with interface to C1, C2, C3 Div 1/Zone 0
Marine certification	ABS, BV, DNV, LR
Temperature, Operating	0 to +55 °C (+32 to +131 °F)
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)
Pollution degree	Degree 2, IEC 60664-1
Corrosion protection	ISA-S71.04: G3
Relative humidity	5 to 95 %, non-condensing
Max ambient temperature	55 °C (131 °F), for vertical mounting in compact MTU 40 °C (104 °F)
Protection class	IP20 according to IEC 60529
Mechanical operating conditions	IEC/EN 61131-2
EMC	EN 61000-6-4, EN 61000-6-2
Overvoltage categories	IEC/EN 60664-1, EN 50178
Equipment class	Class I according to IEC 61140; (earth protected)
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)
WEEE compliance	DIRECTIVE/2012/19/EU

Compatibility	
Use with MTU	TU890, TU891
Keying code	AC

Dimensions	
Width	45 mm (1.77")
Depth	102 mm (4.01"), 111 mm (4.37") including connector
Height	119 mm (4.7")
Weight	0.2 kg (0.44 lbs.)

Related products



TU890



TU891

solutions.abb/800xA
solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2024 ABB All rights reserved