

DOS801

ABB Ability™ System 800xA® hardware selector



Select I/O is an Ethernet networked, single-channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes, and supports standardization of I/O cabinetry ensuring automation projects are delivered on time and under budget. A Signal Conditioning Module (SCM) performs the necessary signal conditioning and powering of the connected field device for one I/O channel.

The DOS801 is a Digital Output (24V / 0.6A) Signal Conditioning Module supporting 2-wire devices.

Features and benefits

- Digital output for 2-wire field devices
- 24 V / 0.6 A current sourcing
- Can be used in hazardous areas
- Field power sourced from the power injection
- Short circuit proof, electronically current limited to 0.6 A
- Built-in inductive load suppression, free-wheeling diode
- Galvanic isolation
- Protected against wrong wiring
- Diagnostics:
 - Loop supervision (open circuit and short circuit)
 - Communication supervision
 - Internal power supervision
 - Power injection supervision
- OSP (Output Set to Predetermined value)
- Single loop granularity - each SCM handles a single channel
- Supports hot swap
- Mechanical locking slider which turns off field device power and/or output before removal.
- Field disconnect function which can galvanically separate the field loop wiring from the SCM during commissioning and maintenance.
- All SCMs have electronic current limitation
- Mechanical keying to prevent insertion of wrong module type after commissioning.
- 24 V DC powered through Modulebus
- Configurable through parameters
- LED indicators on the SCM indicate the operational state of the module

General info	
Article number	2PAA123604R1
Type	Digital Output Module
Number of channels	1
Signal specification	24 V DC / 0.6 A
HART	N/A
SOE	N/A
Redundancy	No
Hot swap	Yes
High integrity	No
Intrinsic safety	No
Mechanics	Select I/O

Detailed data	
Supported field devices	2-wire
Isolation	Galvanic isolation to system. Routine tested at factory with 2000 VDC.
Field power	Current limited
Diagnostics	Loop supervision (short circuit and open circuit) Communication supervision Internal power supervision Power injection supervision
Calibration	Factory calibration
Power dissipation	0.51 W
Installation in Hazardous Area/Locations	Yes/Pending
IS barrier	No
Output load. Max inductor time constant (L/R)	40 - 5000 Ω, 50 ms
Field Input Robustness	±35 V between all terminals
Input voltage range	19.2 ... 30 V

Environment and certification	
Temperature, Operating	-40 °C (-40 °F) to +70 °C (158 °F)
Temperature, Storage	-40 °C (-40 °F) to +85 °C (185 °F)
Pollution degree	Pollution Degree 2 acc. to IEC 60664-1
Relative humidity	5 to 95 %, non-condensing
Altitude	-1000 to 5000 m (restrictions apply)
Mechanical operating conditions	IEC 61131-2
EMC	IEC/EN 61000-6-4, IEC/EN 61000-6-2
Overvoltage categories	Category II acc. to IEC 60664-1
Protection class	IP20 acc. to IEC 60529
CE-marking	Yes
UKCA	Yes
Electrical Safety	IEC/EN 61010-1 UL 61010-1 CSA-C22.2 No. 61010-1-12 IEC/EN 61010-2-201 UL 61010-2-201 CSA C22.2 No. 61010-2-201
Marine certification	N/A
Corrosive atmosphere	G3
RoHS compliance	EU RoHS, UAE RoHS, CN RoHS
WEEE compliance	EU
Hazardous Area ATEX	II 3G Ex ec IIC T4 Gc
Hazardous Area IECEx	II 3G Ex ec IIC T4 Gc
Hazardous Location US/CAN	Pending
Hazardous Area CCC	Ex ec IIC T4 Gc

Dimensions	
Width	77.9 mm
Depth	105 mm
Height	9.8 mm
Weight (including base)	54 g

solutions.abb/800xA
solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved