

# TC811

## ABB Ability™ System 800xA® hardware selector



Select I/O is an Ethernet networked, single channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes, and supports standardization of I/O cabinetry ensuring automation projects are delivered on time and under budget. A Signal Conditioning Module (SCM) performs the necessary signal conditioning and powering of the connected field device for one I/O channel.

TC811 is an Ethernet Adapter for fiber optic media with a built-in 2-port switch. Hosts two LC ports. For redundant configuration two Fieldbus Communication Interfaces CI845, two Ethernet Adapters TC811, and one TU860 or one TU865 are needed.

### Features and benefits

- Can be used as single or redundant
- Supports both Select I/O and S800 on Ethernet
- Hosts two LC ports
- Built-in switch
- Built-in diagnostics
- Supports hot swap
- Can be used in hazardous area
- Mechanical locking slider which turns off power before removal
- Mechanical keying
- LED indicators

General info	
Article number	3BSE078714R1
Communication protocol	Ethernet
Type	Ethernet Adapter for fiber optic media
HART	N/A
SOE	N/A
Redundancy	Yes
Hot swap	Yes
High integrity	N/A
Intrinsic safety	N/A
Mechanics	Select I/O
Type of external output	100 BASE-FX with LC connector
Number of external ports	2
Type of connecting cable	9/125 µm single mode fiber (1310 nm nominal wavelength)
Maximum length of cable	27.5 km

Detailed data	
Isolation	Galvanic isolation between Ethernet/power supply and I/O modules
Power dissipation	2 W
24 V consumption typ.	80 mA
Installation in Hazardous Area/Locations	Yes/Yes (on IPA)

Environment and certification	
Temperature, Operating	-40 °C (-40 °F) to +65 °C (149 °F)
Temperature, Storage	-40 °C (-40 °F) to +85 °C (185 °F)
Pollution degree	Pollution Degree 2 acc. to IEC 60664-1
Relative humidity	5 to 95 %, non-condensation
Altitude	-1000 to 5000 m (restrictions apply)
Mechanical operating conditions	IEC 61131-2
EMC	IEC/EN 61000-6-4, IEC/EN 61000-6-2
Overvoltage categories	Category II acc. to IEC 60664-1
Protection class	IP20 acc. to IEC 60529
CE-marking	Yes
UKCA	Yes
Electrical Safety	IEC/EN 61010-1 UL 61010-1 CSA-C22.2 No. 61010-1-12 IEC/EN 61010-2-201 UL 61010-2-201 CSA C22.2 No. 61010-2-201
Marine certification	DNV, ABS
Corrosive atmosphere	G3
RoHS compliance	EU RoHS, UAE RoHS, CN RoHS
WEEE compliance	EU
Hazardous Area ATEX	II 3G Ex ec IIC T4 Gc II 3G Ex ic ec IIC T4 Gc
Hazardous Area IECEx	Available on IPA: II 3G Ex ec IIC T4 Gc II 3G Ex ic ec IIC T4 Gc
Hazardous Location US/CAN	Available on IPA: cULus CL I, ZN 2, AEx ec IIC T4 Gc, Ex ec IIC T4 Gc X CL I, DIV 2, Groups A-D T4
Hazardous Area CCC	Ex ec IIC T4 Gc Ex ec ic IIC T4 Gc

Dimensions	
Width	24.5 mm
Depth	101.3 mm
Height	110 mm
Weight (including base)	161 g

---

**[solutions.abb/800xA](https://solutions.abb/800xA)**  
**[solutions.abb/controlsystems](https://solutions.abb/controlsystems)**

---

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved