


TU834

ABB Ability™ System 800xA® hardware selector



The TU834 MTU can have up to 8 I/O channels and 2+2 process voltage connections. Each channel has two I/O connections and one ZP connection. Input signals are connected via individual shunt sticks, TY801. The maximum rated voltage is 50 V and maximum rated current is 2 A per channel. The MTU distributes the ModuleBus to the next MTU. It also generates the correct address to the I/O modules by shifting the outgoing position signals to the next MTU.

The MTU can be mounted on a standard DIN rail. It has a mechanical latch that locks the MTU to the DIN rail.

Features and benefits

- Complete installation of I/O modules using 2-wire connections and field power distribution.
- Up to 8 channels of field signals and process power connections.
- Mechanical keying prevents insertion of the wrong I/O module.
- Latching device to DIN rail for grounding.
- DIN rail mounting.
- Include 8 individual shunt sticks.

| General info | |
|----------------------|---|
| Article number | 3BSE040364R1 |
| Type | Extended |
| Connection | Terminal block |
| Channels | 8 |
| Voltage | 50 V |
| Mounting | Both directions |
| Mounting detail | 55 °C (131 °F) |
| Use with I/O | AI880 and AI880A |
| Process connections | 40 up to 8 I/O channels (2 terminals per channel) 4 Process power 20 Process power (0 V) |
| Single/redundant I/O | Single |

| Detailed data | |
|------------------------------------|---|
| Maximum current per I/O channel | 2 A |
| Maximum current process connection | 5 A |
| Acceptable wire sizes | Solid: 0.2 - 4 mm ² Stranded: 0.2 - 2.5 mm ² , 24 - 12 AWG Recommended torque: 0.5 - 0.6 Nm Stripping length: 7 mm |
| Dielectric test voltage | 500 V a.c. |

| Environment and certification | |
|---------------------------------|---|
| CE mark | Yes |
| Electrical safety | EN 61010-1, UL 61010-1, EN 61010-2-201, UL 61010-2-201 |
| Hazardous Location | C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2 |
| Marine certification | ABS, BV, DNV-GL, LR |
| Temperature, Operating | 0 to +55 °C (+32 to +131 °F), approvals are issued for +5 to +55 °C |
| Temperature, Storage | -40 to +70 °C (-40 to +158 °F) |
| Pollution degree | Degree 2, IEC 60664-1 |
| Corrosion protection | ISA-S71.04: G3 |
| Relative humidity | 5 to 95 %, non-condensing |
| Max ambient temperature | 55 °C (131 °F) |
| Protection class | IP20 according to IEC 60529 |
| Mechanical operating conditions | IEC/EN 61131-2 |
| EMC | EN 61000-6-4, EN 61000-6-2 |
| Overvoltage categories | IEC/EN 60664-1, EN 50178 |
| Equipment class | Class I according to IEC 61140; (earth protected) |
| RoHS compliance | EN 50581:2012 |
| WEEE compliance | DIRECTIVE/2012/19/EU |

| Dimensions | |
|------------|--|
| Width | 126 mm (5.0 in.) including connector, 120.5 mm (4.74 in.) edge to edge installed |
| Depth | 64 mm (2.52 in.) including terminals |
| Height | 110 mm (4.3 in.) including locking device |
| Weight | 0.28 kg (0.6 lbs) |

solutions.abb/800xA
solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved