

DATA SHEET

## **DO801**

## ABB Ability™ System 800xA® hardware selector



The DO801 is a 16 channel 24 V digital output module for the S800 I/O. The output voltage range is 10 to 30 volt and the maximum continuous output current is 0.5 A. The outputs are protected against short circuits, over voltage and over temperature. The outputs are in one isolated group. Each output channel consists of a short circuit and over temperature protected high side driver, EMC protection components, inductive load suppression, output state indication LED and optical isolation barrier.

## Features and benefits

- 16 channels for 24 V d.c. current sourcing outputs
- 1 isolated groups of 16 channels
- Output status indicators
- OSP sets outputs to predetermined state upon communication error
- Short-circuit protection to ground and 30 V
- Over-voltage and overtemperature protection
- Process and power connection via detachable connectors

General info		
Article number	3BSE020510R1	
Туре	Digital Output	
Signal specification	24 V d.c. (12 - 32 V d.c.), 0.5 A	
Number of channels	16	
Signal type	Current sourcing, current limiting	
HART	No	
SOE	No	
Redundancy	No	
High integrity	No	
Intrinsic safety	No	
Mechanics	S800L	

Detailed data		
Isolation	Groupwise isolated from ground	
Output load	< 0.4 Ω	
Current limiting	Short circuit proof current limited output	
Maximum field cable length	600 meters (656 yards)	
Rated insulation voltage	50 V	
Dielectric test voltage	500 V a.c.	
Power dissipation	Typ. 2.1 W	
Current consumption +5 V Modulebus	80 mA	
Current consumption +24 V Modulebus	0	
Current consumption +24 V external	0	
Supported wire size	Solid: 0.05-2.5 mm², 30-12 AWG Stranded: 0.05-1.5 mm², 30-12 AWG Recommended torque: 0.5-0.6 Nm Stripping length 6-7.5mm, 0.24-0.30 inch	

Diagnostics		
Front LED's	S(tatus), Channel 1-16 Status	
Status indication of supervision	Module Error, Module Warning, Channel Error	

Environment and certification	
CE mark	Yes
Electrical safety	EN 61010-1, UL 61010-1, EN 61010-2-201, UL 61010-2-201
Hazardous Location	C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2
Marine certification	ABS, BV, DNV, LR
Temperature, Operating	0 to +55 °C (+32 to +131 °F), approvals are issued for +5 to +55 °C
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)
Pollution degree	Degree 2, IEC 60664-1
Corrosion protection	ISA-S71.04: G3
Relative humidity	5 to 95 %, non-condensing
Max ambient temperature	55 °C (131 °F), for vertical mounting 40 °C (104 °F)
Protection class	IP20 according to IEC 60529
Mechanical operating conditions	IEC/EN 61131-2
EMC	EN 61000-6-4, EN 61000-6-2
Overvoltage categories	IEC/EN 60664-1, EN 50178
Equipment class	Class I according to IEC 61140; (earth protected)
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions		
Width	86.1 mm (3.4")	
Depth	58.5 mm (2.3")	
Height	110 mm (4.33")	
Weight	0.24 kg (0.53 lbs.)	



solutions.abb/800xA solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved