

GIS880

ABB Ability™ System 800xA® hardware selector



Select I/O is an Ethernet networked, single channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes, and supports standardization of I/O cabinetry ensuring automation projects are delivered on time and under budget. A Signal Conditioning Module (SCM) performs the necessary signal conditioning and powering of the connected field device for one I/O channel.

GIS880 a Generic I/O Module for High Integrity. Certified for SIL3. Use as single or redundant.

Features and benefits

- Distribution of process I/O data between the SCMs and the FCI
- Mechanical locking slider which turns off the power supplies before removal
- Supports hot swap
- Mechanical keying to prevent insertion of wrong module type
- Can be used in hazardous areas
- Certified for SIL3
- LED indicators:
 - Status (S)
 - Primary (P)
- Diagnostics:
 - Hardware error supervision
 - Communication supervision
 - Internal power supervision

General info

Article number	3BSE075855R1
Type	Generic I/O Module High Integrity
HART	Yes
SOE	Yes
Redundancy	Yes
Hot swap	Yes
High integrity	Yes
Intrinsic safety	N/A
Mechanics	Select I/O

Detailed data

Diagnostics	Internal hardware supervision Communication supervision Internal power supervision
Power dissipation	0.4 W
Installation in Hazardous Area/Locations	Yes/Yes

Environment and certification

Temperature, Operating	-40 °C (-40 °F) to +70 °C (158 °F)
Temperature, Storage	-40 °C (-40 °F) to +85 °C (185 °F)
Pollution degree	Pollution Degree 2 acc. to IEC 60664-1
Relative humidity	5 to 95 %, non-condensation
Altitude	-1000 to 5000 m (restrictions apply)
Mechanical operating conditions	IEC 61131-2
EMC	IEC/EN 61000-6-4, IEC/EN 61000-6-2
Overtoltage categories	Category II acc. to IEC 60664-1
Protection class	IP20 acc. to IEC 60529
CE-marking	Yes
UKCA	Yes
Electrical Safety	IEC/EN 61010-1 UL 61010-1 CSA-C22.2 No. 61010-1-12 IEC/EN 61010-2-201 UL 61010-2-201 CSA C22.2 No. 61010-2-201
Marine certification	DNV, ABS
Corrosive atmosphere	G3
RoHS compliance	EU RoHS, UAE RoHS, CN RoHS
WEEE compliance	EU
Hazardous Area ATEX	II 3G Ex nA IIC T4 Gc II 3G Ex ec IIC T4 Gc II 3G Ex ic nA IIC T4 Gc II 3G Ex ic ec IIC T4 Gc
Hazardous Area IECEx	Available on IPA: II 3G Ex nA IIC T4 Gc II 3G Ex ec IIC T4 Gc II 3G Ex ic nA IIC T4 Gc II 3G Ex ic ec IIC T4 Gc
Hazardous Location US/CAN	cULus CL I, ZN 2, AEx ec IIC T4 Gc, Ex ec IIC T4 Gc X CL I, ZN 2, AEx nA IIC T4 Gc, Ex nA IIC T4 Gc X CL I, DIV 2, Groups A-D T4
Hazardous Area CCC	Ex ec IIC T4 Gc Ex ec ic IIC T4 Gc
Functional Safety	IEC 61508 Ed. 2, SIL 1-3 IEC 61511-1 IEC 62061 IEC 61131-2, IEC 61131-6 IEC 60204-1 NFPA 72, NFPA 79, NFPA 85, NFPA 86 EN ISO 14118 EN 50156-1 EN 298 EN 54-2, EN 54-2 A1 EN ISO 13850

Dimensions

Width	77.9 mm
Depth	108 mm
Height	15.8 mm
Weight (including base)	76 g

solutions.abb/800xA
solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved