

DIS821

ABB Ability™ System 800xA® hardware selector



Select I/O is an Ethernet networked, single channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes, and supports standardization of I/O cabinetry ensuring automation projects are delivered on time and under budget. A Signal Conditioning Module (SCM) performs the necessary signal conditioning and powering of the connected field device for one I/O channel.

The DIS821 is a Digital Input 230 V Signal Conditioning Module supporting 2/3/4-wire devices with Sequence of Events (SOE).

Features and benefits

- Digital input for 2-wire, 3-wire, and externally powered 4-wire field devices
- Channel to channel galvanic isolation
- Field power sourced from the power injection
- Configurable software signal filter 0...100 ms
- Diagnostics:
 - Fuse status supervision
 - Communication supervision
 - Internal power supervision
- Sequence of Events (SoE)
- DIS821 supports both Normally Open (NO) and Normally Closed (NC)
- Single loop granularity - each SCM handles a single channel
- Supports hot swap
- Mechanical locking slider which turns off field device power and/or output before removal
- Field disconnect function which can galvanically separate the field loop wiring from the SCM during commissioning and maintenance
- Mechanical keying to prevent insertion of wrong module type after commissioning
- 24 V DC powered through Modulebus
- Configurable through parameters
- LED indicators on the SCM indicate the operational state of the module

| General info | |
|----------------------|----------------------|
| Article number | 2PAA123608R1 |
| Type | Digital Input Module |
| Number of channels | 1 |
| Signal specification | 230 V AC/DC |
| HART | N/A |
| SOE | Yes |
| Redundancy | No |
| Hot swap | Yes |
| High integrity | No |
| Intrinsic safety | No |
| Mechanics | Select I/O |

Detailed data

| | |
|--|---|
| Supported field devices | 2-wire, 3-wire and 4-wire sensors (dry contacts and proximity switches, external power required for 4-wire devices) |
| Isolation | Galvanic isolation to system and between each channel. Routine tested at factory with 3060 VDC. |
| Field power | Current limited through fuse if power injection is used |
| Diagnostics | Fuse status supervision Communication supervision Internal power supervision |
| Calibration | Factory calibration |
| Power dissipation | 0.5 W |
| Installation in Hazardous Area/Locations | No/No |
| IS barrier | No |
| Input voltage range | 164...250 V AC / 175...250 V DC |

Environment and certification

| | |
|---------------------------------|---|
| Temperature, Operating | -40 °C (-40 °F) to +70 °C (158 °F) |
| Temperature, Storage | -40 °C (-40 °F) to +85 °C (185 °F) |
| Pollution degree | Pollution Degree 2 acc. to IEC 60664-1 |
| Relative humidity | 5 to 95 %, non-condensing |
| Altitude | -1000 to 3000 m (restrictions apply) |
| Mechanical operating conditions | IEC 61131-2 |
| EMC | IEC/EN 61000-6-4, IEC/EN 61000-6-2 |
| Overvoltage categories | Category II acc. to IEC 60664-1 |
| Protection class | IP20 acc. to IEC 60529 |
| CE-marking | Yes |
| UKCA | Yes |
| Electrical Safety | IEC/EN 61010-1 UL 61010-1 CSA-C22.2 No. 61010-1-12 IEC/EN 61010-2-201 UL 61010-2-201 CSA C22.2 No. 61010-2-201 |
| Marine certification | N/A |
| Corrosive atmosphere | G3 |
| RoHS compliance | EU RoHS, UAE RoHS, CN RoHS |
| WEEE compliance | EU |
| Hazardous Area ATEX | No |
| Hazardous Area IECEx | No |
| Hazardous Location US/CAN | No |
| Hazardous Area CCC | No |

Dimensions

| | |
|-------------------------|---------|
| Width | 77.9 mm |
| Depth | 105 mm |
| Height | 9.8 mm |
| Weight (including base) | 57 g |

solutions.abb/800xA
solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved