

DATA SHEET

CI853

ABB Ability™ System 800xA® hardware selector



CI853 RS-232 module protocols:

COMLI can be used on the built-in COM3 port and optionally on the CI853 ports. The cable length can be extended considerably (to several km) using a fiber optic converter. RS-232C is the standard communication interface used for serial communication with COMLI. The CI853 supports Hot Swap. COMLI is an ABB protocol for data transmission between controllers. It is designed for asynchronous master/slave communication in half-duplex. COMLI protocol supports dial-up modems controlled from the application. CI853 supports both Master/Slave modes in COMLI.

MODBUS RTU is a standard protocol widely spread because of its ease of use and reliability. Modbus RTU is an open, serial (RS-232 or RS-485) protocol derived from the Master/Slave architecture exchanging information in half duplex mode. The Modbus functionality can be configured both on the COM ports of AC 800M and CI853. Module Redundancy is not available in MODBUS RTU. CI853 supports only Master mode in MODBUS RTU.

Features and benefits

- COMLI can be used on the built-in COM3 port and optionally on the CI853 ports. RS-232C is the standard communication interface used for serial communication with COMLI. The CI853 supports Hot Swap. COMLI is an ABB protocol for data transmission between controllers.
- MODBUS RTU is an open, serial (RS-232) protocol derived from the Master/Slave architecture exchanging information in half duplex mode. The Modbus functionality can be configured both on the COM ports of AC 800M and Cl853.
- Siemens 3964R can be used on the built-in COM3 port and optionally on the CI853 ports. A standard RS-232C/485 communication channel is required.
- Self-defined Serial Communication can be used on the built-in COM3 port (on an AC 800M Controller) and optionally on the CI853 ports.
- The CI853 module also supports Hot Swap.

General info		
Article number	3BSE018103R1 (CI853K01)	
Communication protocol	COMLI and MODBUS RTU	
Master or slave	Master/Slave	
Number of channels	2	
Transmission speed	75 - 19 200 b/s	
Line redundancy	No	
Module redundancy	No	
Hot Swap	Yes	
Used together with HI Controller	Yes	

Detailed data		
Max units on CEX bus	12	
Connector	RJ-45 female (8-pin)	
24 V consumption typ.	100 mA	

Environment and certification		
Temperature, Operating	0 to +55 °C (+32 to +131 °F)	
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)	
Corrosion protection	G3 compliant to ISA 71.04	
Protection class	IP20 according to EN60529, IEC 529	
CE- marking	Yes	
Marine certificates	ABS, BV, DNV-GL, LR	
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)	
WEEE compliance	DIRECTIVE/2012/19/EU	

Dimensions		
Width	59 mm (2.3 in.)	
Height	185 mm (7.3 in.)	
Depth	127.5 mm (5.0 in.)	
Weight (including base)	700 g (1.5 lbs)	



solutions.abb/800xA solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved