

# DIS801

## ABB Ability™ System 800xA® hardware selector



Select I/O is an Ethernet networked, single channel granular I/O system for the ABB Ability™ System 800xA automation platform. Select I/O helps decouple project tasks, minimizes the impact of late changes, and supports standardization of I/O cabinetry ensuring automation projects are delivered on time and under budget. A Signal Conditioning Module (SCM) performs the necessary signal conditioning and powering of the connected field device for one I/O channel.

The DIS801 is a Digital Input 24 V Signal Conditioning Module supporting 2/3/4-wire devices with Sequence of Events (SOE).

### Features and benefits

- Digital input for 2-wire, 3-wire and externally powered 4-wire field devices
- Can be used in hazardous areas
- Field device power output current limited to 35 mA
- Channel to channel galvanic isolation
- Configurable software signal filter 0...100 ms
- Protected against wrong wiring
- Diagnostics:
  - Loop supervision (open circuit and short circuit)
  - Communication supervision
  - Internal power supervision
- Sequence of Events (SoE)
- DIS801 supports both Normally Open (NO) and Normally Closed (NC) 24 V loops
- Single loop granularity - each SCM handles a single channel
- Supports hot swap
- Mechanical locking slider which turns off field device power and/or output before removal
- Field disconnect function which can galvanically separate the field loop wiring from the SCM during commissioning and maintenance
- All SCMs have electronic current limitation
- Mechanical keying to prevent insertion of wrong module type after commissioning
- 24V DC powered through Modulebus
- Configurable through parameters
- LED indicators on the SCM indicate the operational state of the module

## General info

Article number	2PAA123603R1
Type	Digital Input Module
Number of channels	1
Signal specification	24 V DC
HART	N/A
SOE	Yes
Redundancy	No
Hot swap	Yes
High integrity	No
Intrinsic safety	No
Mechanics	Select I/O

## Detailed data

Supported field devices	2-wire, 3-wire and 4-wire sensors (dry contacts and proximity switches, external power required for 4-wire devices)
Isolation	Galvanic isolation to a system and between each channel (including field power). Routine tested at factory with 2000 VDC.
Field power	Current limited to 35 mA
Diagnostics	Loop supervision (short circuit and open circuit) Communication supervision Internal power supervision
Calibration	Factory calibration
Power dissipation	0.45 W
Installation in Hazardous Area/Locations	Yes/Pending
IS barrier	No
Field Input Robustness	±35 V between all terminals
Input voltage range	19.2 ... 30 V

## Environment and certification

Temperature, Operating	-40 °C (-40 °F) to +70 °C (158 °F)
Temperature, Storage	-40 °C (-40 °F) to +85 °C (185 °F)
Pollution degree	Pollution Degree 2 acc. to IEC 60664-1
Relative humidity	5 to 95 %, non-condensation
Altitude	-1000 to 5000 m (restrictions apply)
Mechanical operating conditions	IEC 61131-2
EMC	IEC/EN 61000-6-4, IEC/EN 61000-6-2
Overvoltage categories	Category II acc. to IEC 60664-1
Protection class	IP20 acc. to IEC 60529
CE-marking	Yes
UKCA	Yes
Electrical Safety	IEC/EN 61010-1 UL 61010-1 CSA-C22.2 No. 61010-1-12 IEC/EN 61010-2-201 UL 61010-2-201 CSA C22.2 No. 61010-2-201
Marine certification	N/A
Corrosive atmosphere	G3
RoHS compliance	EU RoHS, UAE RoHS, CN RoHS
WEEE compliance	EU
Hazardous Area ATEX	II 3G Ex ec IIC T4 Gc
Hazardous Area IECEx	II 3G Ex ec IIC T4 Gc
Hazardous Location US/CAN	Pending
Hazardous Area CCC	Ex ec IIC T4 Gc

---

**Dimensions**

---

Width	77.9 mm
Depth	105 mm
Height	9.8 mm
Weight (including base)	54 g

---

—  
[solutions.abb/800xA](https://solutions.abb/800xA)  
[solutions.abb/controlsystems](https://solutions.abb/controlsystems)

—  
800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved