

DATA SHEET

TB846

ABB Ability™ System 800xA® hardware selector



The TB846 redundant ModuleBus Cable Adaptor is used together with TB845 and two TK801V0xx to extend the ModuleBus. Using this extension I/O modules on the same electrical ModuleBus can be mounted on different DIN rails. TB846 can also be used together with TB842 to provide an optical extension of the ModuleBus.

General info		
Article number	3BSE021439R1	
Mechanics	S800	

Environment and certification		
CE mark	Yes	
Electrical safety	IEC 61131-2, UL 61010-1, UL 61010-2-201	
Hazardous Location	C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2	
Marine certification	ABS, BV, DNV, LR	
Temperature, Operating	0 to +55 °C (Storage -25 to +70 °C), RH=5 to 95 % no condensation, IEC/EN 61131-2	
Pollution degree	Degree 2, IEC 60664-1	
Corrosion protection	ISA-S71.04: G3	
Protection class	IP20 according to IEC 60529	
Mechanical operating conditions	IEC 61131-2	
EMC	EN 61000-6-4 and EN 61000-6-2	
Overvoltage categories	IEC/EN 60664-1	
Equipment class	Class I according to IEC 61140; (earth protected)	
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)	
WEEE compliance	DIRECTIVE/2012/19/EU	

Dimensions	
Width	43 mm
Depth	31.5 mm
Height	186 mm
Weight	180 g



solutions.abb/800xA solutions.abb/controlsystems

800xA and Symphony Plus is a registered trademark of ABB. All rights to other trademarks reside with their respective owners.

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved